



Product name:
Melting Point Apparatus

Product code:
CIVIL-CHM-150-0001



Description

Melting Point Apparatus

Technical specification

The heating rate can be adjusted manually between 1 to 20°C/min, and for rapid heating 10°C/min, to obtain an accurate melting point range. The sample and melt process can be viewed via the magnifying lens, which is illuminated by bright LEDs. The measures the melting point of chemicals from ambient to 250°C. Samples need to be placed in a sealed end capillary tube and located in the heating block. Up to three tubes can be tested at one time. Record the melt temperatures from the thermometer, positioned horizontal to the samples to allow simultaneous viewing. The lens can be detached for cleaning and simple to follow instructions are printed directly on to the unit, making it easy for students to use. For 220/240V.



Civil Laboratory Equipment Manufacturers and Suppliers India Civil Lab Exports India

Email us at: export@civilmechanicalindia.com